

VISIONSCAPE® I-PAK®



Packaging Inspection System

The Visionscape I-PAK inspection system is the proven solution chosen by major pharmaceutical manufacturers worldwide. Based on a selection of powerful machine vision tools and a simple user interface, I-PAK meets demanding pharmaceutical industry requirements for reliable, accurate and validated inspection of labels and products.

Typical applications include date/lot code verification, component ID verification, and a variety of other package, label or product inspections.

Visionscape I-PAK: At a Glance

- Robust Optical Character Verification (OCV)
- High speed decoding and verification of 1D/ 2D codes
- 21 CFR Part 11 Compliant
- Available in three versions for flexible implementation



I-PAK SE: High speed, industrial touch screen PC in an IP67 stainless steel enclosure with tilted top, specifically designed for pharmaceutical environments



I-PAK SK: Solution Kit consists of Visionscape board and software, supports up to four progressive scan cameras or one CameraLink digital camera



I-PAK HE: Software CD offers I-PAK interface and functionality for up to four Visionscape Smart Cameras

For more information on this product, visit www.microscan.com.

Powerful Software

Based on the powerful Visionscape software, I-PAK offers a comprehensive selection of proven vision processing tools. The I-PAK user interface makes setup and deployment of applications fast and easy, and allows 100% verification of every product on the line.

FDA Compliance


I-PAK enables manufacturers to comply with FDA's current Good Manufacturing Practices and meets the requirements of 21 CFR Part 11 through user access control features and audit trail capabilities.

Advanced Capabilities

- Print quality and readability of date/lot codes, NDC or other human readable marks
- Inspection of codes on labels, cartons, inserts/outserts or directly marked on products
- Accommodates a variety of marking methods (laser, hot stamp, ink jet)
- Fast and reliable decoding and quality verification of linear barcodes, GS1 Databar (RSS) and Data Matrix
- Fully configurable system for broad range of other product or package inspections

Fail-Safe Identification

I-PAK provides fail-safe identification of incorrect or illegible characters while tolerating normal print variation. Proven robust OCV algorithms adapt to acceptable changes in preprinted or overprinted codes to reduce false rejects.



Sample print quality defects detected by I-PAK

Visionscape I-PAK: Available Codes

Linear	All Standard 	2D Symbols	Data Matrix 	QR
Stacked	PDF417 	Human Readable	User-defined/ trainable Optical Character Recognition (OCR) and Verification (OCV)	
	GS1 Databar 			



I-PAK SK: Specifications for Solution Kit Configuration

MINIMUM PC REQUIREMENTS: I-PAK SK, host for VS0740 or VS0800 PCI board

- Pentium P4 class PC (2.4 GHz or higher)
- Windows 2000 (SP4 or later), Windows XP (SP2 or later)
- 1 GB minimum RAM
- XGA display (True Color or 64K)
- One open PCI slot (for Visionscape Board installation)



I-PAK HE: Specifications for Smart Camera Software Configuration

MINIMUM PC REQUIREMENTS: I-PAK HE, platform for I-PAK HE GUI

- Pentium P4 class PC (2.4 GHz or higher)
- Windows 2000 (SP4 or later), Windows XP (SP2 or later)
- 1 GB minimum RAM
- XGA display (True Color or 64K)
- 100BaseT Ethernet NIC

I-PAK SE: Specifications for Stainless Steel Enclosure Configuration



MECHANICAL: Enclosure

Height: 20.63" (524 mm)
Width: 28.35" (720 mm)
Depth: 8.46" (215 mm)
Weight: 99.2 lbs (45 Kg)

MECHANICAL: Shelf Mount

Height: 5.12" (130 mm)
Depth: 6.14" (156 mm)
Weight: 26.5 lbs (12 Kg)

MECHANICAL: Floor Stand

Height: 19.69" (500 mm)
Width: 19.69" (500 mm)
Depth: 55.19" (1400 mm)
Weight: 66.1 lbs (30 Kg)

COMMUNICATION PROTOCOLS

Interfaces: RS-232, Ethernet TCP/IP

ELECTRICAL

Power Requirement: 115 VAC / 60Hz, 15 Amps max. or 230 VAC / 50Hz, 16 Amps max.

Power Consumption: 140 W max.

SYMBOLGY TYPES

2D Symbolgies: Data Matrix (ECC 0-200), QR Code, Micro QR Code
Stacked Symbolgies: PDF417, GS1 Databar (Composite & Stacked)
Linear Barcodes: Code 39, Code 128, BC 412, I2 of 5, UPC/EAN, Pharmacode, Codabar, Code 93
Human Readable: User-defined/trainable OCR and OCV

ENVIRONMENTAL

Enclosure: Stainless steel, IP67
Operating Temperature: 0° to 40° C (32° to 104° F)
Storage Temperature: 0° to 40° C (32° to 104° F)
Storage: Up to 95% (non-condensing)

DISCRETE I/O

Up to 16 discrete digital I/O points
 4 strobe signals
 4 trigger signals

SAFETY CERTIFICATIONS

FCC, CE

ISO CERTIFICATION

Certified ISO 9001:2008 Quality Management System

©2011 Microscan Systems, Inc. SP037E 01/11
 Performance data is determined using high quality Grade A symbols per ISO/IEC 15415 and ISO/IEC 15416 in a 25°C environment. For application-specific results, testing should be performed with symbols used in the actual application. Microscan Applications Engineering is available to assist with evaluations. Results may vary depending on symbol quality. **Warranty**—One year limited warranty on parts and labor. Free extended 3 year warranty upon online product registration.

MICROSCAN®

Microscan Systems Inc.
 Tel 425 226 5700 / 800 251 7711
 Fax 425 226 8250

Microscan Europe
 Tel 31 172 423360 / Fax 31 172 423366

Microscan Asia Pacific
 Tel 65 6846 1214 / Fax 65 6846 4641

www.microscan.com

Product Information: info@microscan.com
 Auto ID Support: helpdesk@microscan.com
 Vision Support: visionsupport@microscan.com
 NERLITE Support: nerlitesupport@microscan.com